

PU-8-SW**Plastic tubing**

Feature	Data/description
Outside diameter	11 mm
Inside diameter	8 mm
Min. bending radius	84 mm
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-35 - 60 °C
Product weight according to length	0,055 kg/m
Colour	Black
Shore hardness	52 +/- 3
Materials note	Copper and PTFE-free
Materials information for tubing	TPE-U(PU)