



HGL-1/4

Non-return valve

Feature	Data/description
Assembly position	Any
Valve function	piloted non-return function
Operating pressure	0,3 - 10 bar
Standard nominal flow rate	540 l/min
Switching time off	13 ms
Switching time on	7 ms
Operating medium	Dried, filtered compressed air Dried, filtered and lubricated compressed air
Corrosion resistance classification CRC	2
Medium temperature	-20 - 80 °C
Ambient temperature	-20 - 80 °C
Max. tightening torque	20 Nm
Mounting type	Threaded
Pilot air port 21	G1/4
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials information for screw-in stud	Aluminium
Materials information for seals	NBR