

PU-8-DUO-BS**DUO plastic tubing**

Feature	Data/description
Outside diameter	11 mm
Inside diameter	8 mm
Min. bending radius	84 mm
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-35 - 60 °C
Product weight according to length	0,11 kg/m
Colour	blue/black
Shore hardness	52 +/- 3
Materials note	Copper and PTFE-free
Materials information for tubing	TPE-U(PU)