

# Push-in T-fitting NPQP-T-R12-Q12-FD

Part number: 133080

**FESTO**



## Data sheet

Feature	Value
Size	Standard
Nominal size	6.9 mm
Design	T-shape Push-pull principle
Size of pack	1
Operating pressure complete temperature range	-0.095 MPa...0.45 MPa -0.95 bar...4.5 bar -13.775 psi...65.25 psi
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...60 °C
Product weight	28 g
Type of mounting	External hexagon, size 22 mm
Pneumatic connection, port 1	Male thread R1/2
Pneumatic connection, port 2	For tubing outer diameter of 12 mm
Colour of release ring	Transparent white
Note on materials	RoHS-compliant
Material housing	PP
Material tubing clamp component	High-alloy stainless steel