



## VAM-63-V1/9-1/4

### Vacuum gauge

Feature	Data/description
Nominal size of pressure gauge	63
Position of connection	Rear side central
Design structure	Bourdon-tube pressure gauge
Indicating range [bar]	-1 - 9 bar
Indicating range [psi]	-14,5 - 130,5 psi
Operating medium	Compressed air, filtered, unlubricated Filtered, lubricated air
Continuous load factor	0,75
Alternating load factor	0,67
Ambient temperature	-10 - 60 °C
Measurement accuracy class	1,6
Mounting type	Threaded
Pneumatic connection	G1/4
Materials information, housing	Steel Painted
Materials info, viewing window	Glass