



VAM-40-V1/0-1/8

Vacuum gauge

Feature	Data/description
Nominal size of pressure gauge	40
Position of connection	Rear side central
Design structure	Bourdon-tube pressure gauge
Indicating range [bar]	-1 - 0 bar
Indicating range [psi]	-14,5 - 0 psi
Operating medium	Compressed air, filtered, unlubricated Filtered, lubricated air
Continuous load factor	0,75
Alternating load factor	0,67
Ambient temperature	-10 - 60 °C
Measurement accuracy class	1,6
Mounting type	Threaded
Pneumatic connection	G1/8
Materials information, housing	Steel Painted
Materials info, viewing window	Glass