

LFR-1/2-S-7-B

Filter regulator

Data sheet

Part no.: 150038

Page:1

Feature	Data/description
Modular design	Yes
Input pressure 1 min. (bar)	0,5 bar
Input pressure 1 max. (bar)	14 bar
Output pressure 2 max.	7 bar
Thread for port 1	G 1/2
Thread for port 2	G 1/2
Type of mounting	Hole
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	60 °C
Metal bowl guard	No
Grade of filtration	40 µm
Maximum condensate capacity	86 cm³
Condensate drain system	Manual, rotary
Actuator locking (press. reg.)	Pull-up-and-turn adjustment
Pressure hysteresis (pressure regul.)	0,2 bar
Pressure gauge yes/no	Yes
Material of housing	PA-polymer
Material of bowl	PA-polymer
Contains silicone materials	Yes
Standard nominal flow rate 1-2	4710 l/min
Operating medium input 1	Compressed air
Operating medium output 2	Compressed air, filtered 40 µm, unlubricated