

**MFH-5-1/4-NA**

Solenoid valve

Data sheet

Part no.: 150715

Page:1

<b>Feature</b>	<b>Data/description</b>
Switching function short code	<b>5/2</b>
Control type	<b>Monostable</b>
Operating pressure min.	<b>2 bar</b>
Operating pressure max.	<b>10 bar</b>
Type of connection, air supply	<b>Thread</b>
Connecting thread, supply port	<b>G 1/4</b>
Air connection type power port	<b>Sub-base</b>
Type of connection, exhaust	<b>Thread</b>
Connecting thread, exhaust port	<b>G 1/4</b>
Country-specific approval certificate (U	<b>UL(OL)</b>