

MSFW-110AC-EEX

Solenoid coil

Data sheet

Part no.: 151278

Page:1

Feature	Data/description
Minimum ambient temperature	-5 °C
Maximum ambient temperature	40 °C
Voltage type	AC/..
Nominal AC voltage	110
Power consumption - pull (AC)	4,84/4,32
Frequency (AC)	50/60
Duty cycle, solenoid	100 %
Degree of protection	IP65