

FRC-3/4-E

Service unit

Data sheet

Part no.: 15237

Page:1

Feature	Data/description
Modular design	No
Input pressure 1 max. (bar)	16 bar
Output pressure 2 max.	12 bar
Thread for port 1	G 3/4
Thread for port 2	G 3/4
Type of mounting	Hole
Minimum ambient temperature	-10 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	50 °C
Minimum flow for lubricator operation	50 l/min
Design lubricator	Direct proportional
Oil capacity max.	150 cm³
Metal bowl guard	Yes
Grade of filtration	50 µm
Maximum condensate capacity	75 cm³
Condensate drain system	Manual, rotary
Actuator locking (press. reg.)	Pull-up-and-turn adjustment
Pressure gauge yes/no	Yes
Material of housing	Aluminium
Material of bowl	PC-polymer
Standard nominal flow rate 1-2	3200 l/min
Operating medium input 1	Compressed air
Operating medium output 2	Compressed air, filtered 40 µm, lubricated