

Push-in/threaded QSK-M5-3

Part number: 153290

FESTO

Datasheet

Feature	Value
Nominal size tubing connection	3
Thread type	R
Thread diameter (metric)	5 mm
Operating pressure min.	-0,95 bar
Operating pressure max.	10 bar
Minimum ambient temperature	0 Cel
Maximum ambient temperature	60 Cel