



## MEH-3-M5

### Solenoid valve

Feature	Data/description
Nominal size	0,9 mm
Type of actuation	electrical
Sealing principle	soft
Manual override	detenting
Design structure	Poppet seat
Type of reset	mechanical spring
Type of piloting	direct
Flow direction	non reversible
Valve function	3/2 monostable
Standard nominal flow rate	22 l/min
Operating pressure	-0,9 - 8 bar
Operating medium	Filtered, unlubricated compressed air, 50 µm filtration Filtered, lubricated compressed air, 50 µm filtration
Medium temperature	-5 - 50 °C
Ambient temperature	-5 - 50 °C
Mounting type	with through hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Pneumatic connection, port 3	M5
Materials information for seals	NBR
Materials information, housing	Aluminium