



CRQH-DR-1/4-B

Ball valve drive unit

| Feature | Data/description |
|---------------------------------|--|
| Nominal size | 9 mm |
| Type of actuation | manual |
| Sealing principle | soft |
| Design structure | Ball valve |
| Valve function | 2/2 Bistable |
| Operating pressure | 0 - 63 bar |
| Standard nominal flow rate | 5.610 l/min |
| Operating medium | Water Neutral gases Compressed air |
| Medium temperature | -40 - 200 °C |
| Ambient temperature | -40 - 230 °C |
| Product weight | 1.500 g |
| Mounting type | Line installation |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Contains PWIS substances |
| Materials information for cover | Stainless steel casting |
| Materials information for seals | FPM PTFE |
| Materials information, housing | Stainless steel casting |