

Double DPZJ-20-80-P-A-S20-KF

Part number: 160190

FESTO



Datasheet

Feature	Value
Mode of operation	Double acting
Type of mounting	Circlip
Form, external	Profile
Form piston	Round
Form piston rod	Round
Sensing type	Magnetic
Type of cushioning	Internal cushioning ring (non-adjustable)
Protection against torsion	Parallel pistons
Piston, nominal size	20 mm
Stroke	80 mm