

PAN-L-6x1-NT**Plastic tubing**

Feature	Data/description
Ambient temperature	-30 - 80 °C
Operating medium	Filtered compressed air Vacuum
Shore hardness	55 +/- 3
Colour	neutral
Inside diameter	4,000 mm
Outside diameter	6,000 mm
Food-industry approval	90/128/EWG
Materials note	Copper and PTFE-free
Product weight according to length	0,0160 kg/m
Min. bending radius	32,000 mm
Materials information for tubing	TPE-A