

## **KVI-CP-1-GS-WD-8**

### **Connecting cable**

<b>Feature</b>	<b>Data/description</b>
Assembly position	Any
Operating voltage AC	<= 60 V
Permissible current load	3 A
Protection class	IP65
Ambient temperature	-5 - 80 °C -20 - 70 °C
Product weight	412 g
Electrical connection	Plug straight / socket angled
Cable structure	5 x 0,24 mm <sup>2</sup>
Cable diameter	5,2 mm
Cable length	8 m
Mounting type	With sleeve nut
Materials information, housing	Brass Nickel plated
Materials information, cable sheaths	PUR
Materials information, plug	Bronze Gold plated