

CPV18-EPL-PE

End plate

Data sheet

Part no.: 163194

Page:1

| Feature | Data/description |
|-----------------------------|--|
| Type of mounting sub-base | Screw |
| Operating pressure min. | -0,9 bar |
| Operating pressure max. | 16 bar |
| Minimum ambient temperature | -10 °C |
| Maximum ambient temperature | 50 °C |
| Minimum medium temperature | -10 °C |
| Maximum medium temperature | 50 °C |
| CT criterion | Free of copper and PTFE |
| Medium | Dried filtered compressed air (may be lubricated) |