

CPV18-EPL-E

End plate

Data sheet

Part no.: 163196

Page:1

| Feature | Data/description |
|---------------------------------------|--|
| Type of mounting sub-base | Screw |
| Operating pressure min. | -0,9 bar |
| Operating pressure max. | 16 bar |
| Minimum ambient temperature | -10 °C |
| Maximum ambient temperature | 50 °C |
| Minimum medium temperature | -10 °C |
| Maximum medium temperature | 50 °C |
| Air connection type connection 1 | Thread |
| Air connection type connections 3,5 | Thread |
| Air connection type connections 12,14 | Thread |
| Air connection type connections 82,84 | Thread |
| Air connection type connection 11 | Thread |
| Thread for port 1 | G 3/8 |
| Thread for ports 3, 5 | G 1/2 |
| Thread for ports 12, 14 | G 1/4 |
| Thread for ports 82, 84 | G 1/4 |
| Thread for port 11 | G 3/8 |
| CT criterion | Free of copper and PTFE |
| Medium | Dried filtered compressed air (may be lubricated) |