



LFR-3/4-D-O-MAXI-CT

Filter regulator

Feature	Data/description
Size	Maxi
Series	D
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	manual rotary
Design structure	Filter regulator without pressure gauge
Max. condensate volume	80 cm ³
Bowl guard	Metal bowl guard
Pressure gauge	G1/4" prepared
Pressure control range	0,5 - 12 bar
Inlet pressure 1	1 - 16 bar
Max. pressure hysteresis	0,4 bar
Standard nominal flow rate	9.000 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Product weight	1.300 g
Mounting type	with accessories
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 2	G3/4
Materials note	Copper and PTFE-free
Materials information, housing	Zinc die-casting



Data sheet

Part no.: **165837**

Page:2

LFR-3/4-D-O-MAXI-CT

Filter regulator

Feature	Data/description
Materials information for bowl	PC