

KVI-CP-2-GS-GD-2

Connecting cable

Feature	Data/description
Assembly position	Any
Operating voltage AC	<= 60 V
Permissible current load	3 A
Protection class	IP65
Ambient temperature	-5 - 80 °C -20 - 70 °C
Product weight	126 g
Electrical connection	Plug straight / socket straight
Cable structure	5 x 0,24 mm ²
Cable diameter	5,2 mm
Cable length	2 m
Mounting type	With sleeve nut
Materials information, housing	Brass Nickel plated
Materials information, cable sheaths	PUR
Materials information, plug	Bronze Gold plated