


## SME-10-ZS-SL-LED-24

### Proximity Sensor

Feature	Data/description
Ambient temperature	-20 - 70 °C
Mounting type	Clamped in round slot
Product weight	5,000 g
CE Symbol	In compliance with EU directive 89/336/EWG (EMV)
Electrical connection	3-pin Cable with plug M8x1
Cable length	0,300 m
Protection class	IP65 IP67
Ambient temperature	-5,000 - 70,000 °C
Short circuit strength	No
Polarity protected	No
Design	for round slot
Operating voltage DC	12,000 - 27,000 V
Materials information, housing	PPS
Switch-off time	<= 0,050 ms
Max. output current	100,000 mA
Switch-on time	<= 0,600 ms
Switch output	with contact, bipolar Without LED function
Switching element function	Normally open contact
Max. contact rating DC	1,000 W
Voltage drop	3,000 V
Measuring principle	Reed magnetic



## SME-10-ZS-SL-LED-24

### Proximity Sensor

Feature	Data/description
Operating status display	Yellow LED
Materials information, cable sheaths	PUR
Reproducibility of switching value	+/- 0,1 mm