

# pressure regulator LR-3/8-D-7-O-MIDI-NPT


Part number: 173659

Classic - do not use for new projects

Without threaded connection plate, connector thread in housing,  
without pressure gauge

Modern alternatives can be found by entering the first four characters  
of the type code in the search field.

FESTO



## Data sheet

Feature	Value
Size	Midi
Series	D
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Materials note	Conforms to RoHS