

filter

LF-1/2-D-MIDI-NPT


Part number: 173692

Classic - do not use for new projects

[With metal bowl guard.](#)

[Modern alternatives can be found by entering the first four characters of the type code in the search field.](#)

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Midi |
| Series | D |
| Assembly position | Vertical |
| Grade of filtration | 40 µm |
| Condensate drain | manual momentary-contact |
| Max. condensate volume | 43 cm ³ |
| Bowl guard | Metal bowl guard |
| Operating pressure | 0 ... 16 bar |
| Standard nominal flow rate | 3,000 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [:-9:-] Inert gases |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | Compressed air in accordance with ISO8573-1:2010 [7:8:4] Inert gases |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Mounting type | Line installation With mounting bracket Optional |
| Pneumatic connection, port 1 | 1/2 NPT |
| Pneumatic connection, port 2 | 1/2 NPT |
| Materials note | Conforms to RoHS |
| Material filter | PE |
| Material housing | Zinc die-casting |
| Material bowl | PC |