

KDI-SB60-6,0-M12

Programming cable

Feature	Data/description
Assembly position	Any
Operating voltage AC	<= 300 V
Ambient temperature	-10 - 80 °C -30 - 80 °C
Product weight	361 g
Electrical connection	M12x1/SDL 5-pin / 8-pin Plug straight / socket straight
Cable structure	7 x 0,24 mm ²
Cable diameter	5,9 mm
Cable length	6 m
Mounting type	Clip With sleeve nut
Materials information for locknut	Brass Nickel plated
Materials information, housing	PBT
Materials information, cable sheaths	PUR
Materials information, plug	Copper alloy Gold plated