


Round cylinder DSAG-40- -PPV-S2-S6

Part number: 176508


FESTO

End cap with threaded lug, with through piston rod and heat-resistant seals up to 120°C

This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	40 mm
Piston rod thread	M12x1,25
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Piston-rod end	Male thread
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 120 °C
Cushioning length	22 mm
Theoretical force at 6 bar, return stroke	633 N
Theoretical force at 6 bar, advance stroke	754 N
Moving mass with 0 mm stroke	469 g
Additional weight per 10 mm stroke	24 g
Basic weight for 0 mm stroke	586 g
Additional mass factor per 10 mm of stroke	15.9 g
Pneumatic connection	M32x2
Materials information for cover	Wrought Aluminium alloy
Materials information for seals	FPM
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel