

swivel flange SUA-100-R3

Part number: 176891

FESTO

For cylinders ADVU, AEVU; matching clevis foot mountings LBN or LN, LSN.



Data sheet

| Feature | Value |
|---|--|
| Size | 100 |
| Assembly position | Any |
| Variants | Excellent corrosion protection |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 1,236 g |
| Materials note | Conforms to RoHS |
| Material mounting | Wrought Aluminium alloy With protective coating |
| Material mounting pin | High alloy steel, non-corrosive |
| Material sleeve | Spring steel |
| Material bearing | Plastic |
| Material disc | steel, galvanized |
| Material screws | High alloy steel, non-corrosive |
| Material lock | High alloy steel, non-corrosive |
| Material shaft | High alloy steel, non-corrosive |