

Clamping cartridge KP-12-600

Part number: 178456

FESTO



Data sheet

Feature	Value
Assembly position	Any
Type of clamping with direction of action	at both ends Clamping with spring, release with compressed air
Design structure	Tilting disks
Variants	Single-ended piston rod
Operating pressure MPa	≤ 1 MPa
Operating pressure	≤ 10 bar
Release pressure (MPa)	≥ 0.3 MPa
Release pressure (bar)	≥ 3 bar
Round material to be clamped	12 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 80 °C
Static holding force	600 N
Product weight	50 g
Material seals	NBR TPE-U(PU)
Material spring	Spring steel
Material housing	Aluminium Anodised
Material clamp jaws	Brass
Material piston	POM