

LR-M2-G3/8-07K

Pressure regulator

Data sheet

Part no.: 178778

Page:1

Feature	Data/description
Design regulating valve	Diaphragm
Type of regulation	Direct
Regulator function	Output pressure constant
Modular design	Yes
Input pressure 1 max. (bar)	21 bar
Output pressure 2 min.	0 bar
Output pressure 2 max.	7 bar
Air connection type 1	Female thread
Thread for port 1	G 3/8
Air connection type 2	Female thread
Thread for port 2	G 3/8
Installation position	Any
Type of mounting	Front/line/bracket
Minimum ambient temperature	-10 °C
Maximum ambient temperature	80 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	80 °C
Actuator locking	Pull-up-and-turn adjustment
Pressure gauge yes/no	No
Material of operator panel	POM
Material of housing	Die-cast zinc
Material of seals	NBR-Elastomer
Material of diaphragm	NBR: Brass
Contains silicone materials	Yes
Product weight	0,64 kg
Standard nominal flow rate 1-2	4700 l/min
Medium	Compressed air, filtered 40 µm