



LFR-M2-G3/8-E07UG

Filter regulator

Feature	Data/description
Size	2
Series	M
Actuator lock	Rotary knob with lock
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Filter regulator with pressure gauge
Max. condensate volume	54 cm ³
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Pressure control range	0 - 7 bar
Inlet pressure 1	0 - 17 bar
Standard nominal flow rate	5.200 l/min
Operating medium	Compressed air
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	1.219 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting
Materials information for bowl	Zinc die-casting