



## LFR-M3-G3/8-C04S

### Filter regulator

Feature	Data/description
Size	3
Series	M
Actuator lock	Rotary knob with lock
Grade of filtration	5 µm
Condensate drain	fully automatic
Design structure	Filter regulator without pressure gauge
Max. condensate volume	65,5 cm <sup>3</sup>
Bowl guard	Plastic guard
Pressure gauge	G1/4" prepared
Pressure control range	0 - 4 bar
Inlet pressure 1	0 - 12 bar
Standard nominal flow rate	6.000 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Product weight	1.189 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting
Materials information for bowl	PC