

LFR-M3-G3/8-C07S

Filter regulator

Data sheet

Part no.: 179700

Page:1

Feature	Data/description
Modular design	Yes
Input pressure 1 max. (bar)	12 bar
Output pressure 2 min.	0 bar
Output pressure 2 max.	7 bar
Thread for port 1	G 3/8
Thread for port 2	G 3/8
Type of mounting	In-line/bracket
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Minimum medium temperature	-10 °C
Maximum medium temperature	60 °C
Metal bowl guard	No
Grade of filtration	5 µm
Maximum condensate capacity	65,5 cm³
Condensate drain system	Fully automatic
Actuator locking (press. reg.)	Pull-up-and-turn adjustment
Pressure gauge yes/no	No
Material of housing	Die-cast zinc
Material of bowl	PC-polymer
Contains silicone materials	Yes
Product weight	1,189 kg
Standard nominal flow rate 1-2	6800 l/min
Operating medium input 1	Compressed air
Operating medium output 2	Compressed air, filtered 5 µm, unlubricated