



## LFR-M3-G3/8-C04UG

### Filter regulator

| Feature                        | Data/description                                  |
|--------------------------------|---|
| Size                           | 3   |
| Series                         | M   |
| Actuator lock                  | Rotary knob with lock                             |
| Grade of filtration            | 5 µm  |
| Condensate drain               | fully automatic                                   |
| Design structure               | Filter regulator with pressure gauge              |
| Max. condensate volume         | 72,5 cm <sup>3</sup>                              |
| Bowl guard                     | Plastic guard                                     |
| Pressure gauge                 | with pressure gauge                               |
| Pressure control range         | 0 - 4 bar   |
| Inlet pressure 1               | 0 - 17 bar  |
| Standard nominal flow rate     | 6.000 l/min                                       |
| Operating medium               | Compressed air                                    |
| Medium temperature             | -10 - 80 °C                                       |
| Ambient temperature            | -10 - 80 °C                                       |
| Product weight                 | 1.800 g   |
| Mounting type                  | Optional<br>Line installation<br>with accessories |
| Pneumatic connection, port 1   | G3/8  |
| Pneumatic connection, port 2   | G3/8  |
| Materials note                 | Contains PWIS substances                          |
| Materials information, housing | Zinc die-casting                                  |
| Materials information for bowl | Zinc die-casting                                  |