



FRC-M2-G1/2-C07R

Service unit

Feature	Data/description
Size	2
Series	M
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	manual rotary
Design structure	Filter regulator without pressure gauge Proportional standard oil-mist lubricator
Max. condensate volume	52,75 cm ³
Bowl guard	Plastic guard
Pressure gauge	G1/4" prepared
Pressure control range	0 - 7 bar
Inlet pressure 1	<= 12 bar
Max. pressure hysteresis	0,3 bar
Standard nominal flow rate	4.200 l/min
Operating medium	Compressed air
Medium temperature	-10 - 52 °C
Ambient temperature	-10 - 52 °C
Product weight	1.593 g
Mounting type	Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances



FRC-M2-G1/2-C07R

Service unit

Feature	Data/description
Materials information, housing	Zinc die-casting
Materials information for bowl	PA