



FRC-M3-G3/8-E16UG

Service unit

| Feature | Data/description |
|------------------------------|---|
| Size | 3 |
| Series | M |
| Actuator lock | Rotary knob with lock |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | fully automatic |
| Design structure | Filter regulator with pressure gauge Proportional standard oil-mist lubricator |
| Max. condensate volume | 72,5 cm ³ |
| Bowl guard | Plastic guard |
| Pressure gauge | with pressure gauge |
| Pressure control range | 0 - 16 bar |
| Inlet pressure 1 | <= 17 bar |
| Max. pressure hysteresis | 0,4 bar |
| Standard nominal flow rate | 1.600 l/min |
| Operating medium | Compressed air |
| Medium temperature | -10 - 80 °C |
| Ambient temperature | -10 - 80 °C |
| Product weight | 3.395 g |
| Mounting type | Line installation with accessories |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Materials note | Contains PWIS substances |



FRC-M3-G3/8-E16UG

Service unit

| Feature | Data/description |
|--------------------------------|------------------|
| Materials information, housing | Zinc die-casting |
| Materials information for bowl | Zinc die-casting |