



## LF-M3-G3/8-ES

### Filter

| Feature                          | Data/description                           |
|----------------------------------|--|
| Size                             | 3  |
| Series                           | M  |
| Assembly position                | Vertical +/- 5°                            |
| Grade of filtration              | 40 µm                                      |
| Condensate drain                 | fully automatic                            |
| Design structure                 | Sintered filter with centrifugal separator |
| Max. condensate volume           | 65,5 cm <sup>3</sup>                       |
| Bowl guard                       | Plastic guard                              |
| Inlet pressure 1                 | 0 - 12 bar                                 |
| Standard nominal flow rate       | 4.700 l/min                                |
| Operating medium                 | Compressed air                             |
| Medium temperature               | -10 - 60 °C                                |
| Ambient temperature              | -10 - 60 °C                                |
| Mounting type                    | Line installation with accessories         |
| Pneumatic connection, port 1     | G3/8                                       |
| Pneumatic connection, port 2     | G3/8                                       |
| Materials note                   | Contains PWIS substances                   |
| Materials information for filter | PE   |
| Materials information, housing   | Zinc die-casting                           |
| Materials information for bowl   | PP   |