



## LF-M3-G1/2-CR

### Filter

Feature	Data/description
Size	3
Series	M
Assembly position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	manual rotary
Design structure	Sintered filter with centrifugal separator
Max. condensate volume	72,5 cm <sup>3</sup>
Bowl guard	Plastic guard
Inlet pressure 1	0 - 12 bar
Standard nominal flow rate	6.000 l/min
Operating medium	Compressed air
Medium temperature	-10 - 60 °C
Ambient temperature	-10 - 60 °C
Mounting type	Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances
Materials information for filter	PE
Materials information, housing	Zinc die-casting
Materials information for bowl	PP