




LFM-M1-G1/4-BS

Fine filter

Feature	Data/description
Size	1
Series	M
Assembly position	Vertical +/- 5°
Grade of filtration	1 µm
Filter efficiency	99,9999 %
Condensate drain	fully automatic
Design structure	Fibre filter
Max. condensate volume	10 cm ³
Bowl guard	Plastic guard
Inlet pressure 1	0 - 8 bar
Standard nominal flow rate	140 l/min
Operating medium	Compressed air
Storage temperature	-10 - 60 °C
Medium temperature	-10 - 60 °C
Residual oil content	0,5 mg/m ³
Ambient temperature	-10 - 60 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances
Materials information for filter	Boron silicate fibre
Materials information, housing	Zinc die-casting



LFM-M1-G1/4-BS

Fine filter

Feature	Data/description
Materials information for bowl	PA