



LFM-M2-G1/4-AT

Micro filter

Feature	Data/description
Size	2
Series	M
Assembly position	Vertical +/- 5°
Grade of filtration	0,01 µm
Condensate drain	manual rotary
Design structure	Fibre filter
Max. condensate volume	54 cm ³
Bowl guard	Plastic guard
Differential pressure display	Spirit level
Inlet pressure 1	0 - 17 bar
Standard nominal flow rate	400 l/min
Operating medium	Filtered, unlubricated compressed air, 5 µm filtration
Medium temperature	-10 - 60 °C
Residual oil content	0,01 mg/m ³
Ambient temperature	-10 - 60 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances
Materials information for filter	Boron silicate fibre
Materials information, housing	Zinc die-casting
Materials information for bowl	Zinc die-casting