




LFM-M3-G1/2-BR

Fine filter

Feature	Data/description
Size	3
Series	M
Assembly position	Vertical +/- 5°
Grade of filtration	1 µm
Filter efficiency	99,9999 %
Condensate drain	manual rotary
Design structure	Fibre filter
Max. condensate volume	65,5 cm3
Bowl guard	Plastic guard
Differential pressure display	Spirit level
Inlet pressure 1	0 - 12 bar
Standard nominal flow rate	1.000 l/min
Operating medium	Filtered, unlubricated compressed air, 5 µm filtration
Storage temperature	-10 - 60 °C
Medium temperature	-10 - 60 °C
Residual oil content	0,5 mg/m3
Ambient temperature	-10 - 60 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances
Materials information for filter	Boron silicate fibre



LFM-M3-G1/2-BR

Fine filter

Feature	Data/description
Materials information, housing	Zinc die-casting
Materials information for bowl	PA