



LOE-M2-G1/2-Q

Lubricator

Feature	Data/description
Size	2
Series	M
Assembly position	Vertical +/- 5°
Design structure	Proportional standard oil-mist lubricator
Max. oil capacity	113,5 cm ³
Bowl guard	Plastic guard
Inlet pressure 1	0 - 17 bar
Minimum flow rate for lubricator function	20 l/min
Standard nominal flow rate	7.500 l/min
Operating medium	Filtered, unlubricated compressed air, 40 µm filtration
Medium temperature	-10 - 80 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 - 80 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting
Materials information for bowl	Zinc die-casting