



Data sheet

Part no.: **182973**

Page:1

FRM-M2-G1/2-Y

Branching module

Feature	Data/description
Assembly position	Any
Operating pressure	≥ 21 bar
Standard nominal flow rate	10.000 l/min
Operating medium	Compressed air
Storage temperature	-10 - 80 °C
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	264 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances