


HEA-M3-G1/2

Manual on-off valve

Feature	Data/description
Exhaust-air function	not throttleable
Type of actuation	manual
Sealing principle	soft
Assembly position	Any
Manual override	None
Design structure	Flat slide
Flow direction	non reversible
Valve function	3/2 Bistable
Operating pressure	0 - 12 bar
b value	0,6
C value	35 l/sbar
Standard nominal flow rate	10.000 l/min
Operating medium	Compressed air
Corrosion resistance classification CRC	2
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	499 g
Mounting type	Line installation
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Pneumatic connection, port 3	Non-ducted
Materials note	Contains PWIS substances



HEA-M3-G1/2

Manual on-off valve

Feature	Data/description
Materials information for seals	NBR
Materials information, housing	Zinc die-casting