


# Multi-pin plug socket IMP1-SD-25

Part number: 18317

FESTO



## Data sheet

Feature	Value
Permissible cable diameter	11 ... 21 mm
Assembly position	Any
Operating voltage range AC	$\leq 300$ V
Operating voltage range DC	$\leq 250$ V
Permissible current load	10 A
Protection class	IP65
Ambient temperature	-40 ... 125 °C
Product weight	315 g
Terminal cross-section	1.5 mm <sup>2</sup>
Electrical connection	Plug socket 25-pin
Cable gland connection	Pg21
Mounting type	With clamp strap
Materials information, housing	Plastic Die-cast light alloy
Material information for crimp connectors	Copper alloy Silver plated