



LD-M3-G1/2-ECO-3 Diaphragm air dryer

| Feature | Data/description |
|--------------------------------|---|
| Size | 3 |
| Series | M |
| Assembly position | Vertical +/- 5° |
| Design structure | Membrane dryer |
| Inlet pressure 1 | 4 - 10 bar |
| Standard nominal flow rate | 200 l/min |
| Atmospheric dew point | -20 °C |
| Operating medium | Compressed air, filtered, unlubricated |
| Pressure dew point | -20 °C |
| Storage temperature | 5 - 50 °C |
| Medium temperature | 5 - 50 °C |
| Ambient temperature | 5 - 50 °C |
| Product weight | 1.900 g |
| Mounting type | Optional Line installation with accessories |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | G1/2 |
| Materials note | Contains PWIS substances |
| Materials information, housing | Zinc die-casting |
| Materials information for bowl | Wrought Aluminium alloy |