

low consumption air gun LSP-1/4-C

Part number: 184318

FESTO

Made of plastic.



Data sheet

Feature	Value
Exhaust-air function	Air jet can be dosed
Operating pressure	0 ... 10 bar
Standard nominal flow rate	120 l/min
PWIS conformity	VDMA24364 zone III
Sound pressure level	90 dB(A)
Ambient temperature	-10 ... 50 °C
Product weight	125 g
Pneumatic connection	Female thread 1/4
Material housing	PA6 reinforced