


Round cylinder CRDSW-2"- -P-A

Part number: 185386


FESTO

Corrosion resistant,
for proximity sensing, in combi design. With elastic cushioning rings in
end positions.

This product is only available if ordered from the Festo Corporation, USA.
Type to be discontinued. Available until 2012.



Exemplary representation



Data sheet

Feature	Value
Stroke	0.4 ... 20 "
Piston diameter	2"
Based on the standard	ISO 6431
Cushioning	P: Flexible cushioning rings/plates at both ends
Operating pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	4
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	990 N
Theoretical force at 6 bar, advance stroke	1,178 N
Pneumatic connection	NPT1/4-18
Materials information for cover	High alloy steel, non-corrosive
Materials information for seals	TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive