

connecting cable KM12-M12-GSWD-1-4

Part number: 185499

FESTO



Data sheet

Feature	Value
Assembly position	Any
Operating voltage range AC	≤ 60 V
Operating voltage range DC	≤ 75 V
Permissible current load	3.8 A
Protection class	IP67
Ambient temperature with flexible cable installation	-5 ... 70 °C
Ambient temperature	-30 ... 70 °C
Product weight	66 g
Electrical connection	Cable 4-core Plug straight / socket angled M12x1 / M12x1 4-pin / 4-pin
Cable structure	4x0,34
Cable length	1 m
Mounting type	Threaded
Cable sheath colour	Grey
Materials information, housing	TPE-U(PU)
Materials information, cable sheaths	TPE-U(PU)