

CPV14-EPR-PEU

End plate

Data sheet

Part no.: 188457

Page:1

| Feature | Data/description |
|-----------------------------------|-------------------------|
| Air connection type | Sub-base |
| Operating pressure min. | 0 bar |
| Operating pressure max. | 10 bar |
| Minimum ambient temperature | -5 °C |
| Maximum ambient temperature | 50 °C |
| Sound pressure level | 82 dB(A) |
| Standard nominal flow rate | 9000 l/min |
| Material of shock absorber insert | PE |