

Local controller DLP-VSE-2-5/2-C

Part number: 188463

FESTO

For DLP cylinder series.



Data sheet

| Feature | Value |
|---|---|
| Mounting type | Optional with through hole with accessories |
| Outdoor use | C1 - weather protected locations of use |
| Operating pressure | 3 ... 8 bar |
| Nominal operating pressure | 6 bar |
| Operating voltage range DC | 20.4 ... 28.8 V |
| Max. current consumption | 120 mA |
| CE mark (see declaration of conformity) | to EU directive for EMC |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Corrosion resistance classification CRC | 3 |
| Relative air humidity | 5 - 100 % Condensing |
| Protection class | IP65 in assembled condition to IEC 60529 |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 1,600 g |
| Materials information for cover | Wrought Aluminium alloy Anodised |
| Materials information for seals | NBR |
| Materials information, housing | Wrought Aluminium alloy Anodised |
| Screw material data | Steel Galvanised |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |