

**KDTAM-SB60-3-M12****Cable**

Feature	Data/description
Assembly position	Any
Operating voltage AC	<= 300 V
Ambient temperature	-10 - 80 °C -30 - 80 °C
Product weight	203 g
Electrical connection	5-pin / 9-pin M12x1 / Sub-D Plug straight / socket straight
Cable structure	7 x 0,24 mm <sup>2</sup>
Cable diameter	5,9 mm
Cable length	3 m
Mounting type	with through hole With threaded plug
Materials information for locknut	Brass Nickel plated
Materials information, housing	PUR
Materials information, cable sheaths	PUR
Materials information, plug	Copper alloy Gold plated